

# PT 6-MT - Knife-disconnect terminal block



3212160

<https://www.phoenixcontact.com/us/products/3212160>


Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



6 mm<sup>2</sup>



Push-in




20 A

IEC



500 V

IEC



Knife-disconnect terminal block, nom. voltage: 500 V, nominal current: 20 A, connection method: Push-in connection, Rated cross section: 6 mm<sup>2</sup>, cross section: 0.5 mm<sup>2</sup> - 10 mm<sup>2</sup>, mounting: NS 35/7,5, NS 35/15, color: gray

## Your advantages

- Time-saving conductor connection thanks to tool-free direct-connection technology
- Convenient plugging with lower insertion force
- High conductor pull-out forces due to the spring design
- Vibration-resistant and maintenance-free conductor connection
- Full flexibility thanks to the standardized CLIPLINE complete bridging, marking, and testing accessories
- Convenient separation of circuits through the implementation of knife disconnection
- Optimized for manual and automated wiring

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3212160       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE22          |
| Product key                          | BE2231        |
| GTIN                                 | 4055626390598 |
| Weight per piece (including packing) | 19.36 g       |
| Weight per piece (excluding packing) | 18.286 g      |
| Customs tariff number                | 85369010      |
| Country of origin                    | CN            |

# PT 6-MT - Knife-disconnect terminal block



3212160

<https://www.phoenixcontact.com/us/products/3212160>

## Technical data

### Product properties

|                       |                           |
|-----------------------|---------------------------|
| Product type          | Disconnect terminal block |
| Product family        | PT                        |
| Number of connections | 2                         |
| Number of rows        | 1                         |
| Potentials            | 1                         |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 1.31 W |

### Connection data

|                                                                                           |                                                                                                                       |
|-------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Number of connections per level                                                           | 2                                                                                                                     |
| Nominal cross section                                                                     | 6 mm <sup>2</sup>                                                                                                     |
| Connection method                                                                         | Push-in connection                                                                                                    |
| Stripping length                                                                          | 10 mm ... 12 mm                                                                                                       |
| Internal cylindrical gage                                                                 | A5                                                                                                                    |
| Connection in acc. with standard                                                          | IEC 60947-7-1                                                                                                         |
| Conductor cross-section rigid                                                             | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>                                                                            |
| Cross section AWG                                                                         | 20 ... 8 (converted acc. to IEC)                                                                                      |
| Conductor cross-section flexible                                                          | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>                                                                            |
| Conductor cross-section, flexible [AWG]                                                   | 20 ... 8 (converted acc. to IEC)                                                                                      |
| Conductor cross-section flexible ultrasound-compressed                                    | 0.34 mm <sup>2</sup> ... 10 mm <sup>2</sup>                                                                           |
| Conductor cross-section, flexible [AWG] ultrasound-compressed                             | 22 ... 8 (converted acc. to IEC)                                                                                      |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>                                                                             |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>                                                                             |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> When using TWIN ferrules, we recommend a minimum ferrule length of 13 mm. |
| Nominal cross section                                                                     | 6 mm <sup>2</sup>                                                                                                     |
| Nominal current                                                                           | 20 A                                                                                                                  |
| Maximum load current                                                                      | 20 A (with 10 mm <sup>2</sup> conductor cross-section, rigid)                                                         |
| Nominal voltage                                                                           | 500 V                                                                                                                 |

### Connection cross sections directly pluggable

|                                                                   |                                          |
|-------------------------------------------------------------------|------------------------------------------|
| Conductor cross-section rigid                                     | 1 mm <sup>2</sup> ... 10 mm <sup>2</sup> |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 1 mm <sup>2</sup> ... 6 mm <sup>2</sup>  |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 1 mm <sup>2</sup> ... 6 mm <sup>2</sup>  |

## Dimensions

# PT 6-MT - Knife-disconnect terminal block



3212160

<https://www.phoenixcontact.com/us/products/3212160>

|                    |         |
|--------------------|---------|
| Width              | 8.2 mm  |
| Height             | 74.1 mm |
| Depth              | 43.8 mm |
| Depth on NS 35/7,5 | 43.7 mm |
| Depth on NS 35/15  | 51.2 mm |

## Material specifications

|                                                                         |                 |
|-------------------------------------------------------------------------|-----------------|
| Color                                                                   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group                                               | I               |
| Insulating material                                                     | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Electrical tests

### Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 7.3 kV      |
| Result                | Test passed |

### Temperature-rise test

|                                                  |                                     |
|--------------------------------------------------|-------------------------------------|
| Requirement temperature-rise test                | Increase in temperature $\leq 45$ K |
| Result                                           | Test passed                         |
| Short-time withstand current 2.5 mm <sup>2</sup> | 0.3 kA                              |
| Result                                           | Test passed                         |

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 1.89 kV     |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Mechanical tests

# PT 6-MT - Knife-disconnect terminal block



3212160

<https://www.phoenixcontact.com/us/products/3212160>

## Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

## Attachment on the carrier

|                         |             |
|-------------------------|-------------|
| DIN rail/fixing support | NS 35       |
| Test force setpoint     | 5 N         |
| Result                  | Test passed |

## Test for conductor damage and slackening

|                                |                              |
|--------------------------------|------------------------------|
| Rotation speed                 | 10 rpm                       |
| Revolutions                    | 135                          |
| Conductor cross-section/weight | 0.5 mm <sup>2</sup> / 0.3 kg |
|                                | 6 mm <sup>2</sup> / 1.4 kg   |
|                                | 10 mm <sup>2</sup> / 2 kg    |
| Result                         | Test passed                  |

## Environmental and real-life conditions

### Aging

|                    |             |
|--------------------|-------------|
| Temperature cycles | 192         |
| Result             | Test passed |

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |                                                  |
|------------------------|--------------------------------------------------|
| Specification          | DIN EN 50155 (VDE 0115-200):2008-03              |
| Spectrum               | Long life test category 1, class B, body mounted |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$   |
| ASD level              | 0.964 (m/s <sup>2</sup> )/Hz                     |
| Acceleration           | 0.58g                                            |
| Test duration per axis | 5 h                                              |
| Test directions        | X-, Y- and Z-axis                                |
| Result                 | Test passed                                      |

### Shocks

|                                |                                     |
|--------------------------------|-------------------------------------|
| Specification                  | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape                    | Half-sine                           |
| Acceleration                   | 5g                                  |
| Shock duration                 | 30 ms                               |
| Number of shocks per direction | 3                                   |
| Test directions                | X-, Y- and Z-axis (pos. and neg.)   |
| Result                         | Test passed                         |

### Ambient conditions

|                                 |                                                                    |
|---------------------------------|--------------------------------------------------------------------|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; |
|---------------------------------|--------------------------------------------------------------------|

# PT 6-MT - Knife-disconnect terminal block



3212160

<https://www.phoenixcontact.com/us/products/3212160>

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
|                                          | for max. short-term operating temperature, see RTI Elec.)                 |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (operation)         | 20 % ... 90 %                                                             |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# PT 6-MT - Knife-disconnect terminal block




3212160

<https://www.phoenixcontact.com/us/products/3212160>

## Drawings

Circuit diagram



# PT 6-MT - Knife-disconnect terminal block



3212160

<https://www.phoenixcontact.com/us/products/3212160>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3212160>

 **CSA**  
Approval ID: 158887

 **EAC**  
Approval ID: RU C-DE.BL08.B.00644

 **cULus Recognized**  
Approval ID: E60425

|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| B |                       |                       |                   |                             |
|   | 300 V                 | 20 A                  | 20 - 8            | -                           |
| C |                       |                       |                   |                             |
|   | 300 V                 | 20 A                  | 20 - 8            | -                           |
| D |                       |                       |                   |                             |
|   | 600 V                 | 5 A                   | 20 - 8            | -                           |

 **EAC**  
Approval ID: KZ7500651131219505

 **CSA**  
Approval ID: 13631

# PT 6-MT - Knife-disconnect terminal block



3212160

<https://www.phoenixcontact.com/us/products/3212160>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250108 |
| ECLASS-15.0 | 27250108 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000902 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PT 6-MT - Knife-disconnect terminal block



3212160

<https://www.phoenixcontact.com/us/products/3212160>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)