

AGK 10-PTPOWER BU - Pick-off terminal block



3260148

<https://www.phoenixcontact.com/us/products/3260148>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pick-off terminal block, nom. voltage: 1000 V, nominal current: 57 A, number of connections: 2, connection method: Push-in connection, Rated cross section: 10 mm², 1 level, cross section: 0.5 mm² - 16 mm², mounting type: on base element, color: blue

Your advantages

- Large-surface marking
- The fully insulated, optionally used pick-off terminal block enables voltage pick-off
- Pick-off terminal block, for snapping into the side insertion funnel

Commercial data

Item number	3260148
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2ZWX
GTIN	4046356779081
Weight per piece (including packing)	22.6 g
Weight per piece (excluding packing)	22.6 g
Customs tariff number	85369010
Country of origin	TR

AGK 10-PTPOWER BU - Pick-off terminal block



3260148

<https://www.phoenixcontact.com/us/products/3260148>

Technical data

Notes

General	For use with PTPOWER 50, 95, 150, and 185 PowerTurn high-current terminal blocks
General	
Note	The max. load current must not be exceeded by the total current of all connected conductors.

Product properties

Product type	Pick-off terminal
Number of connections	2
Number of rows	1
Potentials	1
Insulation characteristics	
Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.82 W

Connection data

Number of connections per level	2
Nominal cross section	10 mm ²

1 level

Connection method	Push-in connection
Stripping length	18 mm
Internal cylindrical gage	A6
Conductor cross-section rigid	0.5 mm ² ... 16 mm ²
Cross section AWG	20 ... 6 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 16 mm ²
Conductor cross-section, flexible [AWG]	20 ... 6 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 10 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 10 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm ² ... 4 mm ²
Nominal cross section	10 mm ²
Nominal current	57 A
Maximum load current	57 A (The maximum load current must not be exceeded by the total current of all connected conductors.)
Nominal voltage	1000 V AC 1500 V DC

1 level Connection cross sections directly pluggable

AGK 10-PTPOWER BU - Pick-off terminal block



3260148

<https://www.phoenixcontact.com/us/products/3260148>

Conductor cross-section rigid	1 mm ² ... 16 mm ²
Conductor cross-section flexible (ferrule without plastic sleeve)	4 mm ² ... 10 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	2.5 mm ² ... 10 mm ²
Conductor cross-section flexible, with TWIN ferrule with plastic sleeve	2.5 mm ² ... 4 mm ²

Ex data

Rated data (ATEX/IECEx)

Identification	Ex II 2 GD Ex eb IIC Gb
Operating temperature range	-60 °C ... 110 °C
Ex-certified accessories	1204517 SZF 1-0,6X3,5
Ex temperature increase	40 K (51 A / 10 mm ²)
Rated insulation voltage	1000 V
output	(Permanent)

Ex level General

Rated voltage	1100 V
Rated current	50 A
Maximum load current	50 A
Contact resistance	1.05 mΩ

Ex connection data General

Ferrule length	18 mm
Stripping length	18 mm
Nominal cross section	10 mm ²
Rated cross section AWG	6
Connection capacity rigid	0.5 mm ² ... 16 mm ²
Connection capacity AWG	20 ... 6
Conductor cross-section flexible, with ferrule without plastic sleeve min.	1.5 mm ²
Conductor cross-section flexible, with ferrule without plastic sleeve max.	10 mm ²
Single conductor/terminal point, flexible, with ferrule, without plastic sleeve, AWG	20 ... 8

Dimensions

Width	18.5 mm
Height	35 mm
Depth	34.7 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C

AGK 10-PTPOWER BU - Pick-off terminal block



3260148

<https://www.phoenixcontact.com/us/products/3260148>

Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Test voltage setpoint	9.8 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 10 mm ²	1.2 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	2.2 kV AC
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Test for conductor damage and slackening

Rotation speed	9 rpm
Revolutions	135
Conductor cross-section/weight	0.5 mm ² / 0.3 kg
	10 mm ² / 2 kg
	16 mm ² / 2.9 kg
Result	Test passed

Environmental and real-life conditions

Aging

Temperature cycles	192
Result	Test passed

3260148

<https://www.phoenixcontact.com/us/products/3260148>

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	EN 50155:2021-07
Spectrum	Long life test category 1, class B, body mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
ASD level	$0.964 \text{ (m/s}^2\text{)}^2\text{/Hz}$
Acceleration	5.72 m/s^2
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Pulse shape	Half-sine
Acceleration	50 m/s^2
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	on base element
---------------	-----------------

AGK 10-PTPOWER BU - Pick-off terminal block

3260148

<https://www.phoenixcontact.com/us/products/3260148>



Drawings

Circuit diagram



AGK 10-PTPOWER BU - Pick-off terminal block



3260148

<https://www.phoenixcontact.com/us/products/3260148>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3260148>

 CSA Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B	600 V	57 A	20 - 6	-
C	600 V	57 A	20 - 6	-

 cUL Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
C	1000 V	57 A	20 - 6	-

 UL Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
E	1000 V	57 A	20 - 6	-

 EAC Approval ID: RU C-DE.BL08.B.00644				
---	--	--	--	--

 EAC Ex Approval ID: RU C-DE.Ax07.B.03227				
--	--	--	--	--

 IECEx Approval ID: IECExSEV14.0013U				
---	--	--	--	--

 ATEX Approval ID: SEV14ATEX0156U				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
Only rigid conductors	1100 V	50 A	-	0.5 - 16
multi-stranded with ferrule	1100 V	50 A	-	0.5 - 10

AGK 10-PTPOWER BU - Pick-off terminal block



3260148

<https://www.phoenixcontact.com/us/products/3260148>



CCC

Approval ID: 2020322313000630



UKCA-EX

Approval ID: CML 22UKEX1227U



IECEx

Approval ID: IECExSEV14.0013U



EAC Ex

Approval ID: KZ 7500525010101950

AGK 10-PTPOWER BU - Pick-off terminal block



3260148

<https://www.phoenixcontact.com/us/products/3260148>

Classifications

ECLASS

ECLASS-13.0	27250308
ECLASS-15.0	27250308

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

AGK 10-PTPOWER BU - Pick-off terminal block



3260148
<https://www.phoenixcontact.com/us/products/3260148>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.201 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com