

ILB BT ADIO MUX - Wireless set

2702875

<https://www.phoenixcontact.com/us/products/2702875>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wireless MUX set, two modules with 16 digital inputs and outputs and 2 analog inputs and outputs (0 mA ... 20 mA, 0 V ... 10 V) each, RSMA (female) antenna connection, without antennas. Product is being prepared for compliance with the Cyber Resilience Act (CRA).

Product description

The Wireless MUX transmits 16 digital and 2 analog signals bidirectionally. The Wireless MUX is supplied ready to use: Unpack – connect – switch on – and you have a working wireless path.

Your advantages

- Wireless diagnostics by means of bar graph
- Range of 50 m ... 100 m in industrial halls with omnidirectional antennas and up to 400 m outdoors with directional antennas
- Quick connection establishment and signal transmission
- Current Bluetooth 4.0 technology
- Plug and play - startup without configuration
- It couldn't be simpler: unpack – connect – switch on



Commercial data

Item number	2702875
-------------	---------

ILB BT ADIO MUX - Wireless set



2702875

<https://www.phoenixcontact.com/us/products/2702875>

Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN26
Product key	DNC662
GTIN	4055626369846
Weight per piece (including packing)	645.6 g
Weight per piece (excluding packing)	630 g
Customs tariff number	85176200
Country of origin	DE

Technical data

Notes

Note on application	Only for industrial use
Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Product properties

Product type	Wireless module
Product family	Inline
Application	I/O
Type	Stand-alone
MTTF	1458 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	557 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	219 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)
Special properties	The product is being prepared for compliance with the Cyber Resilience Act (CRA)
Diagnostics messages	Short-circuit or overload of the digital outputs LED
	Wireless connection FS LED
	Logic and actuator voltage LED
	Link quality of the wireless connection 4 LEDs

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Times

Delay time	≤ 10 ms (Latency, typical)
	≤ 800 ms (Failsafe function for wireless interruption)

Electrical properties

Maximum power dissipation for nominal condition	1.44 W
---	--------

Supply: Module electronics

Connection method	Inline connector
Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30.5 V DC (via power connector)
Current consumption	60 mA (at 24 V DC, at 25 °C)
Protective circuit	Polarity protection, surge protection

Input data

ILB BT ADIO MUX - Wireless set



2702875

<https://www.phoenixcontact.com/us/products/2702875>

Analog:

Input name	Analog inputs
Description of the input	Single ended
Number of inputs	2
Protective circuit	Surge voltage; Suppressor diodes in the analog inputs, current limitation via internal protective circuit
Measured value resolution	12 bits
Current input signal	0 mA ... 20 mA
Input resistance current input	50 Ω
Voltage input signal	0 V ... 10 V
Input resistance of voltage input	130 k Ω

Digital:

Input name	Digital inputs
Number of inputs	16
Connection method	Spring-cage connection
Connection technology	1-conductor
Input voltage range "0" signal	< 5 V
Input voltage range "1" signal	> 15 V
Nominal input voltage U_{IN}	24 V DC
Permissible conductor length to the sensor	100 m
Typical input current per channel	2.3 mA

Output data

Analog:

Output name	Analog outputs
Number of outputs	2
DAC resolution	12 bit
Current output signal	0 mA ... 20 mA
Load/output load current output	$\leq 500 \Omega$
Voltage output signal	0 V ... 10 V
Load/output load voltage output	$\geq 2 \text{ k}\Omega$

Digital:

Output name	Digital outputs
Connection method	Spring-cage connection
Connection technology	1-conductor
Number of outputs	16
Protective circuit	Short-circuit protection, overload protection, protected against reverse voltages
Output current	8 A
Maximum output current per channel	500 mA
Nominal output voltage	24 V DC
Output current when switched off	$\leq 10 \mu\text{A}$ (When not loaded, a voltage can be measured even at an output that is not set.)

Nominal load, inductive	12 VA (1.2 H, 50 Ω)
Nominal load, lamp	12 W
Nominal load, ohmic	12 W (48 Ω)
Behavior with overload	Auto restart
Behavior with inductive overload	Output can be destroyed
Behavior at voltage switch-off	The output follows the power supply without delay
Reverse voltage resistance to short pulses	Reverse voltage proof
Resistance to permanent reverse voltage	≤ 2 A
Overcurrent shut-down	≥ 0.7 A

Connection data

Conductor cross-section, rigid	0.2 mm² ... 1.5 mm²
Conductor cross-section, flexible	0.2 mm² ... 1.5 mm²
Conductor cross-section, flexible [AWG]	... 16
Stripping length	8 mm

Interfaces

Functions

Wireless licenses	Europe, USA, Canada, additional countries in the e-shop
-------------------	---

Wireless

Modulation type	GFSK (Gaussian Frequency Shift Keying)
Antenna connection method	RSMA (female)
No. of channels	40
Frequency range	2.402 GHz ... 2.48 GHz (ISM bandwidth)
Frequency band	2.4 GHz
Wireless standard	Bluetooth
Transmission power	5 dBm
Receiver sensitivity	-95.00 dBm

Signaling

Diagnostic messages

Diagnostics	Short-circuit or overload of the digital outputs
Message	LED

Diagnostic messages

Diagnostics	Wireless connection
Message	FS LED

Diagnostic messages

Diagnostics	Logic and actuator voltage
Message	LED

Diagnostic messages

Diagnostics	Link quality of the wireless connection
-------------	---

ILB BT ADIO MUX - Wireless set



2702875


<https://www.phoenixcontact.com/us/products/2702875>

Message

4 LEDs

Dimensions

Dimensional drawing



Width

95 mm

Height

123.4 mm

Depth

57 mm

Note on dimensions

with connectors

Material specifications

Color (Housing)

green (RAL 6021)

Material (Housing)

PA 6.6-FR

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)

-25 °C ... 60 °C

Degree of protection

IP20

Air pressure (operation)

795 hPa ... 1080 hPa (up to 2000 m above sea level)

Air pressure (storage/transport)

66 kPa ... 108 kPa (up to 3500 m above sea level)

Ambient temperature (storage/transport)

-25 °C ... 85 °C

Permissible humidity (operation)

95 % (non-condensing)

Permissible humidity (storage/transport)

95 %

Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6

5g

Shock in accordance with EN 60068-2-27/IEC 60068-2-27

25g, 11 ms period, half-sine shock pulse

Approvals

CE

Certificate

CE-compliant

UL, USA/Canada

Identification

508 Listed

Wireless approval, Europe

Note

RED 2014/53/EU

Wireless approval USA, FCC

Identification

YG3ADIOMUX

ILB BT ADIO MUX - Wireless set



2702875

<https://www.phoenixcontact.com/us/products/2702875>

Note	FCC directive, part 15.247
Wireless approval India, WPC	
Certificate	NR-ETA/5957
Wireless approval Japan, MIC	
Identification	Japan MIC (RF) ID:202-LSF002
Wireless approval Canada, IC	
Certificate	4720B-ADIOMUX
Note	ISC directive RSS 210
Wireless approval Mexico, IFT	
Certificate	IFT RCPHIL19-2130
Wireless approval South Africa, ICASA	
Certificate	TA-2006/032
KC approval for South Korea	
Certificate	MSIP-CRI-PCK-2884208

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Electrostatic discharge	
Standards/regulations	EN 61000-4-2
Electrostatic discharge	
Contact discharge	± 6 kV (Test Level 3)
Discharge in air	± 8 kV (Test Level 3)
Comments	Criterion B
Electromagnetic HF field	
Standards/regulations	EN 61000-4-3
Electromagnetic HF field	
Frequency range	26 MHz ... 3 GHz (Test Level 3)
Field intensity	10 V/m
Comments	Criterion A
Fast transients (burst)	
Standards/regulations	EN 61000-4-4
Fast transients (burst)	
Input	± 2 kV (Test Level 3)
Signal	± 2 kV (Signal line)
Comments	Criterion B
Surge current load (surge)	
Standards/regulations	EN 61000-4-5

Surge current load (surge)

Input	± 0.5 kV (symmetrical)
	± 1 kV (asymmetrical)
Signal	± 1 kV (Signal line, asymmetrical)
Comments	Criterion B

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Conducted interference

Frequency range	0.15 MHz ... 80 MHz
Comments	Criterion A
Voltage	10 V

Emitted interference

Emitted radio interference in acc. with EN 55011	EN 55016-2-3 Class A industrial applications
--	--

Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.

Standards and regulations

Protection class	III
Free from substances that could impair the application of coating	VDMA 24364:2018-05

RED

Standard designation	RED directive 2014/53/EU
Standards/specifications	EN 300328
	EN 61000-6-4
	EN 61000-6-2
	EN 62311
	EN 60950

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

ILB BT ADIO MUX - Wireless set


2702875

<https://www.phoenixcontact.com/us/products/2702875>




Drawings


Dimensional drawing



Dimensional drawing



Connection diagram



Device connections


ILB BT ADIO MUX - Wireless set

2702875

<https://www.phoenixcontact.com/us/products/2702875>




Schematic diagram




Function elements

Schematic diagram




Connecting cables

Schematic diagram



Mounting

Block diagram



Basic circuit diagram

ILB BT ADIO MUX - Wireless set



2702875

<https://www.phoenixcontact.com/us/products/2702875>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702875>



UL Listed

Approval ID: E140324



cUL Listed

Approval ID: E140324

FCC

Approval ID: YG3ADIOMUX

Industry Canada

Approval ID: 4720B-ADIOMUX



MIC

Approval ID: 202-LSF002

ILB BT ADIO MUX - Wireless set



2702875

<https://www.phoenixcontact.com/us/products/2702875>

Classifications

ECLASS

ECLASS-13.0	27242602
ECLASS-15.0	27242602

ETIM

ETIM 10.0	EC001597
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c231924d-cc82-48cf-a0b7-ccc5db945e37

EF3.1 Climate Change

CO2e kg	37.37 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com